


GE Basic Bath Fan

BF60 Specifications



RATING

- 60 CFM / 3.5 sones @ 0.10" wg
- 120V, 0.9A, 60 Hz

APPLICATION

- Acceptable for use over tub or shower when installed in a GFCI-protected branch circuit

GRILL

- White polymeric grill secured in place with torsion springs; easily removed if necessary
- Dimensions: 10" x 10"

BLOWER WHEEL

- One-piece polymeric wheel
- 4 1/2" diameter, 1" wide, 10 fins

MOTOR

- Single coil, plug-in, 2 pole
- Lifetime lubrication, thermally protected
- 120V, 60 Hz, 0.9A

FAN HOUSING

- 23 gauge galvanized metal
- Dimensions: 7 3/8" x 7 1/2" x 3 3/4"
- Double metal thickness mounting tabs

DUCT COLLAR

- Plastic collar for 3" duct connection
- Built-in non-metallic damper for quiet operation

UNIT MOUNTING

- Rated for ceilings insulated to R-40
- Designed for ceiling or wall mounting on joists sized down to 2" x 4"
- Maximum drywall thickness: 3/4"
- Rough-in opening: 7 3/4" x 7 3/4"

EFFECTIVE SQ. FT.

- Bathrooms: up to 60 square feet
- Other rooms: up to 75 square feet

SHIPPING

- Box dimensions: 10 3/4" x 10 1/3" x 4 3/4"
- Unit weight: 4 1/2 lbs.
- Cube: 0.29
- Pallet: 96
- UPC: 7 83164 32921 6

STANDARDS

- UL-507 (Electric Fans)
- CSA C22.2 No. 113 (Fans & Ventilators)
- HVI Certified (Standard 916 Air Flow Test & Standard 915 Procedure for Loudness Rating of Residential Fan Products)



HVI PERFORMANCE DATA

	Static pressure (inches of wg)								
	0	0.05	0.1	0.15	0.2	.025	.03	.035	.04
CFM	67	65	61	55	50	44	30	13	10
RPM	2209	2359	2598	2655	2690	2732	2722	2708	2692
Watts	69	65	63	62	62	62	62	62	62



GE Industrial Systems

General Electric Company
41 Woodford Avenue, Plainville, CT 06062
www.GEindustrial.com

© 2003 General Electric Company